



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7842MD 40A 2P SNGL PH Ac Motor Disconnet

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 7842MD |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Double-Pole, Single Phase Switch (7842), 40 Amps, 600VS |
| Weight per unit | 0.3100 (lbs/each) |
| Product Category | Misc Wiring Devices |

Features

| | |
|------------------|-------------------|
| actuator | Toggle |
| amperage rating | 40 |
| connection | Side & Back Wired |
| load | 40A |
| operating cycles | 50000 |
| Poles | 2 |
| Voltage | 600.0 V |
| Voltage Rating | 600 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Color | Black |
| Finish | Matte |

Dimensions and Weight

| | |
|------|--|
| Size | 1.753" Depth x 1.8255" Width x 2.375" Height |
|------|--|

Descriptions

| | |
|------------------------|--|
| Description | 40A 2P SNGL PH AC MOTOR DISCONNENET |
| extra long description | P&S 7842MD 40A 2P SNGL PH AC MOTOR |
| Long Description | Double-Pole, Single Phase Switch (7842), 40 Amps, 600Vs |
| Product Type | 40A 2P SNGL PH Ac Motor Disconnet |
| Special Features | Double Pole, Single Phase Switch, Canada Only Motor Disconnect |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007267716 |
| Manufacturers Part Number | 7842-MD |
| UPC | 785007267716 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | Manual Controller |

Trade Size

| | |
|----------|------|
| Amperage | 40.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.31 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Commercial/Industrial |
| environmental conditions | UL94 V2 |
| Frequency Rating | 60Hz |
| Mounting | BOX |
| Operating Temperature | Maximum continuos +75°C, minimum -40°C |
| standard | CULUS, CSA Listed, UL Listed |