


MASTER-BAND® BLADES

Maximum Performance for Portable Band Saws



Blade Specifications (3 per pack)

TPI	Length (Inches)	Width (Inches)	Thickness (Inches)	Product Number	Cuts Material
10/14	44-7/8	1/2	.023	80114-38-EW-10/14	1/4" & larger
14	44-7/8	1/2	.023	80115-38-EW-14	3/16" - 3/8"
14/18	44-7/8	1/2	.023	80112-38-EW-14/18	1/8" - 5/16"
18	44-7/8	1/2	.023	80116-38-EW-18	3/32" - 1/4"
24	44-7/8	1/2	.023	80117-38-EW-24	up to 1/8"
8/12	44-7/8	1/2	.025	80143-385-EW-8/12	3/8" - 1/2"
10/14	44-7/8	1/2	.025	80144-385-EW-10/14	1/4" & larger
14	44-7/8	1/2	.025	80145-385-EW-14	3/16" - 3/8"
14/18	44-7/8	1/2	.025	80142-385-EW-14/18	1/8" - 5/16"
18	44-7/8	1/2	.025	82310-385-EW-18	3/32" - 1/4"
10/14	53-3/4	1/2	.023	80119-45-EW-10/14	1/4" & larger
14	53-3/4	1/2	.023	80120-45-EW-14	3/16" - 3/8"
14/18	53-3/4	1/2	.023	80123-45-EW-14/18	1/8" - 5/16"
18	53-3/4	1/2	.023	80121-45-EW-18	3/32" - 1/4"
24	53-3/4	1/2	.023	80122-45-EW-24	up to 1/8"
10/14	53-3/4	1/2	.025	80146-455-EW -10/14	1/4" & larger
14/18	53-3/4	1/2	.025	80147-455-EW-14/18	1/8" - 5/16"
6/10	54	1/2	.025	80148-54-EW-6/10	1/2" & larger
8/12	54	1/2	.025	80723-54-EW-8/12	3/8" - 1/2"
10/14	54	1/2	.025	80724-54-EW-10/14	1/4" & larger
14/18	54	1/2	.025	80141-54-EW-14/18	1/8" - 5/16"
18	54	1/2	.025	80150-54-EW-18	3/32" - 1/4"

THE LENOX® ADVANTAGE™

- **Enhanced beam strength**
.023 thick material increases blade strength and reduces deflection and twist.
- **Shatter resistant**
Bi-metal blades bend and resist breaking and extend blade life.
- **Longer lasting**
LENOX® *TUFF TOOTH™* design reinforces tooth for longer blade life.



Blade Specifications (25 per pack)

TPI	Length (Inches)	Width (Inches)	Thickness (Inches)	Product Number	Cuts Material
10/14	44-7/8	1/2	.023	09403-B38EW-10/14	1/4" & larger
14	44-7/8	1/2	.023	09404-B38EW-14	3/16" - 3/8"
14/18	44-7/8	1/2	.023	09407-B38EW-14/18	1/8" - 5/16"
18	44-7/8	1/2	.023	09405-B38EW-18	3/32" - 1/4"
24	44-7/8	1/2	.023	09406-B38EW-24	up to 1/8"
8/12	44-7/8	1/2	.025	09398-B385EW-8/12	3/8" - 1/2"
10/14	44-7/8	1/2	.025	09399-B385EW-10/14	1/4" & larger
14	44-7/8	1/2	.025	09400-B385EW-14	3/16" - 3/8"
14/18	44-7/8	1/2	.025	09401-B385EW-14/18	1/8" - 5/16"
18	44-7/8	1/2	.025	09402-B385EW-18	3/32" - 1/4"
10/14	53-3/4	1/2	.023	09412-B45EW-10/14	1/4" & larger
14	53-3/4	1/2	.023	09413-B45EW-14	3/16" - 3/8"
14/18	53-3/4	1/2	.023	09416-B45EW-14/18	1/8" - 5/16"
18	53-3/4	1/2	.023	09414-B45EW-18	3/32" - 1/4"
24	53-3/4	1/2	.023	09415-B45EW-24	up to 1/8"