



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1810 N. Interstate 35 E
75134-0000, TX Lancaster
Phone: 469-913-1947
Fax: 469-913-1948



812DC2 3" 90 Degree Flexible Metal Conduit Conn

Nsi Industries

Catalog Number	812DC2
Manufacturer	Nsi Industries
Description	Connector, 90 Degrees, Zinc Die Cast, Flex Size 3 Inch
Weight per unit	4.0 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	90 DEG
Connector Type	FMC
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	3
------	---

Descriptions

Description	3" 90 DEGREE FLEXIBLE METAL CONDUIT CONN
extra long description	BPT 812-DC2 3 IN 90 Deg Fmc Connect
Long Description	Connector, 90 Degrees, Zinc Die Cast, Flex Size 3 Inch
Product Type	3 In 90 Deg FMC Connector, Box Of 5

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747158123
Manufacturers Part Number	812-DC2
UPC	781747158123

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	3
------------	---

Packaging

Carton	5
Weight Per each	4

Uses, Certifications, and Standards

Application	90 Degrees connector suitable for used to connect flexible metal conduit to box or enclosure.
standard	UL, CSA