



82548

F54T5 841/HO/ALTO (PK X 40)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Miniature Bi-Pin (G5)

Coating: Copolymer

Color Temperature: 4100 K

Diameter: 0.63 IN

Lamp Type: Fluorescent

Mean Design Lumens: 4450

Package Weight: 12.95 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Voltage: 120 V

Average Life Hours: 24000

Bulb: T5

Color: 841

CRI: 85

Initial Lumens: 5000

Length: 46.00 IN

Package (LxWxH): 46.75 IN x 6.75 IN x 4.25 IN

Pack By: 40

Special Features: Shatter-Resistant

UPC: 726585825486

Wattage: 54.0 W

ULEPH,ROHS,NSF Splash Zone