



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



839511 Vinyl Insul Feml Disconn 22-18AWG, .110", 25/Box

Ideal

| | |
|------------------|---|
| Catalog Number | 839511 |
| Manufacturer | Ideal |
| Description | Ideal, Disconnect Terminal, Vinyl Insulated, Wire Size: 22 - 18 Awg, Voltage Rating: 300 V, Material: Brass, Finish: Tin-Plated, Insulation: 0.150 In Diameter, Connection: Female, Tab Size: 0.110 In X 020 In, Temperature Rating: 75 Deg C |
| Weight per unit | 0.0040 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|-------------------|
| connection | Female |
| insulation | 0.150 IN Diameter |
| Material | Brass |
| Voltage Rating | 300 |
| Wire Size | 22 - 18 |

Material, Color, and Finish

| | |
|--------|------------|
| Finish | Tin-Plated |
|--------|------------|

Descriptions

| | |
|------------------------|---|
| Description | VINYL INSUL FEML DISCONN 22-18AWG, .110", 25/BOX |
| extra long description | IDEAL 83-9511 TRM QCK DISC VINL22-1 |
| Features | Butted seam-construction prevents splitting under maximum pressureInternal barrel serrations grip wires tightly to resist pull-out and reduce electrical resistanceTin-plated brass construction for corrosion resistanceShouldered barrel insulation quickly positions terminal for proper crimpingExpanded insulation entry accommodates a wide variety of insulation diameters and provides additional insulation supportThe complete line of IDEAL crimp terminals, disconnects, and splices offer the right product for an |
| Long Description | IDEAL, Disconnect Terminal, Vinyl Insulated, Wire Size: 22 - 18 AWG, Voltage Rating: 300 V, Material: Brass, Finish: Tin-Plated, Insulation: 0.150 IN Diameter, Connection: Female, Tab Size: 0.110 IN X 020 IN, Temperature Rating: 75 DEG C |
| Product Type | TRM QCK Disc VINL22-18AWG-25PK |
| Special Features | Features: Tin-Plated Brass Construction For Corrosion Resistance; Brazed Or Butted Seams Prevent Splitting; Funnel Entry Insulators; Beveled Barrel Openings Provide Easy Wire Entry; Clearly Marked Wire And Stud Ranges; Color-Coded Insulation; Tab Size: 0.110 IN X 020 IN; Temperature Rating: 75 DEG C |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250490585 |
| Manufacturers Part Number | 839511 |
| UPC | 783250490585 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------|
| Category Description | DISCONNECTS |
| Type | Vinyl Insulated |

Availability

| | |
|-------------|----|
| minimum qty | 25 |
|-------------|----|

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Weight Per each | 0.004 |

Uses, Certifications, and Standards

| | |
|----------|------------------|
| standard | CUL Listed, RoHS |
|----------|------------------|