



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



85340 3GHZ F-Type Femi-to-Femi Coax Splice Adptr 10/Card

Ideal

| | |
|------------------|--|
| Catalog Number | 85340 |
| Manufacturer | Ideal |
| Description | Ideal 85-340 F-Splice Adapter, Connection: F |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Connecting Devices - Adapters |

Features

| | |
|------------|---|
| connection | F |
|------------|---|

Descriptions

| | |
|------------------------|--|
| Description | 3GHZ F-TYPE FEML-TO-FEML COAX SPLICE ADPTR 10/CARD |
| extra long description | IDEAL 85-340 3GHZ F-81 FEM SPLICE A |
| Features | Use the 3GHz F-Splice Adapter for extending coaxial cable runs for all cable and satellite TV applications including High Definition. Attach F-connectors to both ends of the barrel splice to join the cables together. Best for High Definition applications. Nickel plated brass construction. For 750 applications up to 3GHz. Accepts male F connectors on both sides. High bandwidth 0MHz to 3GHz for standard and high definition applications. Long body style for wallplate upgrades. < 0.25 dB insertion loss to maintain signal str |
| Long Description | Ideal 85-340 F-Splice Adapter, Connection: F |
| Product Type | 3GHZ F-81 Fem Splice Adpt 10PK |
| Special Features | High bandwidth; 0 MHz - 3 GHz for standard and high definition applications; Less than 0.25 DB insertion loss, greater than 25 DB return loss |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250853403 |
| Manufacturers Part Number | 85-340 |
| UPC | 783250853403 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | F-Splice Adapter |

Availability

| | |
|-------------|----|
| minimum qty | 10 |
|-------------|----|

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Weight Per each | 0.02 |