



Cutting Oil PC 6180

This non-flammable, water-based cutting oil improves metal cutting operations and increases efficiencies in machining operations.

- USDA H-2
- Reinforced With High-Viscosity Oils And Sulfur-Free Extreme Pressure Additives
- Prolongs Tool life, Reduces Tool Sharpening And Down Time
- Lubricates And Cools At The Cutting Point

| CAT NO | UPC | CAN SIZE | (NET) | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------|----------|-----|------|--------|------|
| 890 | 00890 | 16-oz. Aerosol | (13-oz.) | 12 | 12 | 14.00# | Ea |



Zinc Rich Galvanize PC 6180

Ideal for use on surfaces that are exposed to severe corrosive conditions including structural steel, fencing, automobiles, guard rails, and bridges.

- Contains 97% Pure Zinc Metallic Powder, Which Yields 94% Zinc And 6% Resin Dry Film
- Meets ASTM B-117-64 Salt Spray
- Meets MIL-P-46105 & DOD-P-21035A
- For Temperatures Up To 200°F
- Passed Preece Test For Hot-Dip Galvanizing
- Stops Rust On Steel Or Iron
- Sacrificial Anodization

| CAT NO | UPC | CAN SIZE | (NET) | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------|----------|-----|------|--------|------|
| 7007 | 01417 | 16-oz. Aerosol | (13-oz.) | 12 | 12 | 14.00# | Ea |



Red Insulating Epoxy PC 6180

A tough flexible coating that protects and insulates exposed wires and electrical windings.

- Dries In 15 Minutes; Hard in 1 Hour
- Dielectric Strength Up to 2,270 V/mil
- Excellent Adhesion, High Arc Resistance
- Class F Thermal Resistance
- Resists Oil, Water, Acids, Alkalis
- Penetrates, Coats/Seals In One Step

| CAT NO | UPC | CAN SIZE | (NET) | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------|------------|-----|------|--------|------|
| 401 | 00401 | 16-oz. Aerosol | (12.5-oz.) | 12 | 12 | 14.00# | Ea |



Hornet & Wasp Spray PC 6180

Fast-acting powerful aerosol saturates instantly to eliminate hornets, wasps, and yellow jackets.

- USDA F-2
- Sprays Up To 20 Ft.
- High-Delivery Valve
- High % Active Ingredient
- High Dielectric Strength of 41kV/mm
- EPA Reg. No. 1021-1649
- Lasting Residual Deposit Prevents Reinfestation For Weeks

| CAT NO | UPC | CAN SIZE | (NET) | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------|----------|-----|------|--------|------|
| 862 | 00862 | 20-oz. Aerosol | (15-oz.) | 12 | 12 | 17.00# | Ea |



Applicators & Marking Devices PC 6180

- | | | | |
|---|---|--|--|
| Can Hand'ler: <ul style="list-style-type: none"> • 2-Finger Locking Trigger • Locking Collar | <ul style="list-style-type: none"> • Use With Standard Aerosol Can With 1" Valve Cap | Marking Stick: <ul style="list-style-type: none"> • Approximately 32" Length • Trigger Actuator | <ul style="list-style-type: none"> • Single Hand Operation • Excellent Can Balance |
|---|---|--|--|

| CAT NO | UPC | DESCRIPTION | STD | MSTR | WT/STD | UNIT |
|--------|-------|---------------|-----|------|--------|------|
| 242 | 00242 | Can Hand'ler | 1 | 12 | 0.20# | Ea |
| 245 | 00245 | Marking Stick | 1 | 1 | 2.00# | Ea |

