



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 884SC Encl 8X8X4 N1 PNTD SC *Cooper B-Line/Cable Tray*

|                  |  |
|------------------|--|
| Catalog Number   | 884SC  |
| Manufacturer     | Cooper B-Line/Cable Tray   |
| Description      | Type 1 Screw Cover Enclosure, Steel, Wall Mount, Gray, Painted, 4 In Overall Width, 8 In Overall Length, 8 In Overall Height, 12 Knockouts |
| Weight per unit  | 4.6 (lbs/each)   |
| Product Category | Nema Type 1 Metallic Enclosure   |

### Features

|             |                                   |
|-------------|-----------------------------------|
| Cable Entry | Knockouts                         |
| dimensions  | 8.0000 IN X 4.0000 IN X 8.0000 IN |

### Material, Color, and Finish

|       |      |
|-------|------|
| Color | Gray |
|-------|------|

### Dimensions and Weight

|      |  |
|------|--|
| Size | 8.00 In Width X 4.00 In Depth X 8.00 In Height |
|------|--|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | ENCL 8X8X4 N1 PNTD SC  |
| extra long description | B-LINE 884 SC SC ENC W/ KO 8X8X4   |
| Features               | Eaton's B-Line series junction boxes provide reliable environmental protection and are used as commercial wiring, junction, pull, and termination boxes. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00782051222807 |
| UPC   | 782051222807   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | STEEL JUNCTION BOXES  |
| Type                 | Type 1 junction boxes |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 4.64 |

### Uses, Certifications, and Standards

|             |                       |
|-------------|-----------------------|
| nema rating | 1                     |
| standard    | UL 50,NEMA,CSA C22.2. |