



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



885I Radiant 15A/125V Duplex Recp Iv

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 885I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Sierraplex Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, 2 Gang, #14 to #12 Awg Compatible Wire Size, Wall Mount, 1.29 In Length, 1 In Width, 3.31 In Height, Thermoplastic, Ivory, Impact Resistant, 0.1300 LB |
| Weight per unit | 0.1348 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|----------------|---------------------|
| gang | 2 |
| indoor/outdoor | Indoor |
| insulation | False |
| Outlet Type | Residential, Indoor |
| Poles | 2 |
| Voltage | 125.0 V |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|-----------|--------|
| Size | 4.2 in |
| Thickness | 1 in |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | RADIANT 15A/125V DUPLEX RECP IV |
| extra long description | P&S 885I RADIANT 15A/125V DUP RECEP |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007885019 |
| Manufacturers Part Number | 885I |
| UPC | 785007885019 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 200 |
| Weight Per each | 0.1348 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| environmental conditions | 95% (relative humidity, non-condensing) |
| Mounting | WALL |
| nema rating | 15A |
| standard | UL, CULUS, UL 498 |