



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1612 E. Booth Road
72143-0000, AR Searcy
Phone: 501-368-0309
Fax: 501-368-0619



89212 Terminal Strip, 12-Pole, 22-10 Awg

Ideal

Catalog Number	89212
Manufacturer	Ideal
Description	Terminal Strip, 12 Circuits, 12 Poles, 30 A, 600 V Ac, Steel (Screw) Material, -40 to +260 °F, 7.75 In Overall Length, 1.33 In Overall Width, 0.81 In Overall Height, 0.37 LB
Weight per unit	0.3667 (lbs/each)
Product Category	Power BLKS & Distribution BLKS

Features

amperage rating	30
Spacing	0.562
Wire Size	22 - 10

Descriptions

Description	TERMINAL STRIP, 12-POLE, 22-10 AWG
extra long description	IDEAL 89-212 TERMINAL STRIP 12-CIRC
Special Features	Features: Torque Rating of 16 in-lbs; Rugged base eliminates breakage; Center spacing of 0.562 inch (14.3mm); Accepts up to #10 AWG wire; Corrosion resistant surface plates with #8 phillslot screws; Rated up to 600V, 30A; Accessory jumpers available; Heavy-duty, corrosion-resistant screws, surface plates and optional hardware; Accessory hardware provides a variety of termination options; Available cover helps prevent contact with live terminals; Rugged polyester thermoplastic base (UL Rated 94V-0); Operating

Manufacturer Information

Brand	Ideal
GTIN	00783250892129
UPC	783250892129

Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCK ACCESSORIES
----------------------	----------------------------

Packaging

Carton	1
Weight Per each	0.3667

Uses, Certifications, and Standards

standard	CSA, UL Listed, RoHS
----------	----------------------