



Lumaspec® Dimmers & Fan Speed Controls Rotary Dimmers

Incandescent, Fluorescent & Low Voltage 120VAC, 60 Hz



- 90601
- 90610
- 90611
- 90613
- 93212
- 95600



90621

Features

- Push On/Push Off knob for preset lighting level.
- Full range rotary dimming.
- Low voltage & fluorescent models have field adjustable trims that may be set to control minimum light level.
- Ground lead provided on all models.
- Voltage compensation circuitry in fluorescent & low voltage model reduces lighting fluctuations.
- Fit standard switch plate.
- All dimmers on this page may be ganged without de-rating.

Catalog Number		Description	Color	Ratings
Single Pole	Three Way			
600W Max. Specification Grade-Incandescent, RFI Protected				
90601-L	90603-L	Preset, Push On/Off	Lighted Clear	600W max.
90601-I	90603-I	Preset, Push On/Off	Ivory	600W max.
90601-W	90603-W	Preset, Push On/Off	White	600W max.
600W Max. Commercial Grade-Incandescent				
90610-I	90613-I	Preset, Push On/Off	Ivory	600W max.
90610-W	90613-W	Preset, Push On/Off	White	600W max.
90611-I		Dial, Push On/Off	Ivory	600W max.
90611-W		Dial, Push On/Off	White	600W max.

Catalog Number		Description	Color	Ratings
Single Pole	Three Way			
600W Max. Specification Grade-Incandescent, RFI Protected*				
90621-IDP		Low Profile, Dial On/Off	Ivory	600W max.
90621-WDP		Low Profile, Dial On/Off	White	600W max.

*Available in DynaPak® only.

Catalog Number	Description	Color	Ratings
600VA Max. Specification Grade-Fluorescent, RFI Protected - 120VAC Single Pole			
93212-I	Dial, On/Off	Ivory	600VA max.

For use with 2-12 rapid start 40W fluorescent lamps. Requires dimming ballast.

Catalog Number	Description	Color	Ratings
600VA Max. Specification Grade-Low Voltage, RFI Protected - 120VAC Single Pole			
95600-I	Preset, Push On/Off	Ivory	600VA max.

For use with magnetic transformer incandescent low voltage lighting.

Rotary Dimmer
3-Way Wiring Diagram

