

fiberglass BOX™ Fan & Fixture Support

3-½" & 4" Fan/Fixture Support Box



3-½" Dia.	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fan Rating	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W					
	16.0	9336-NKFR	3-½" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-3/8	3-½	35 lb.	50 lb.	10305	50	23
	20.5	9335-NFR	3-½" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - bulk packed	2-7/8	3-½	35 lb.	50 lb.	41201	50	25
	20.5	9335-NKFR	3-½" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-7/8	3-½	35 lb.	50 lb.	41202	50	25

4" Diameter Fan & Fixture Support	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fan Rating	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W					
	8.0	9370-FR	4" diameter pan fan box, ½" deep base, "pop-in" cable clamp, mounting hardware included	1-½ overall	4	70 lb.	110 lb.	76600	24	6
	14.0	9375-FR	4" diameter thermoplastic fan box, ½" deep base, Speed Klamps™ - molded in, two ½" knockouts, mounting hardware included	3-13/16 overall	4	70 lb.	110 lb.	79291	24	7
	15.0	9364-FANB	4" diameter fan box, adjustable bar hanger, Speed Klamps™ - factory installed	1-11/16	4	35 lb.	50 lb.	99025	20	39
	15.0	9364-KFR	4" diameter bottom mount, Speed Klamps™ - factory installed, mounting hardware included	1-11/16	4	35 lb.	50 lb.	10620	50	21
	15.0	9365-NKFR	4" diameter fan & fixture support, side fetter ring nail mount, "HL" hanger, Speed Klamps™ - factory installed	1-11/16	4	35 lb.	50 lb.	75392	50	29
	16.0	9369-FB	4" diameter fan & fixture support, surface mount, Speed Klamps™ - factory installed, mounting hardware included	1-¾	4	35 lb.	50 lb.	76500	25	12
	16.0	9369-FBH	4" diameter fan box, side mount hanger, Speed Klamps™ - factory installed, mounting hardware included	1-¾	4	35 lb.	50 lb.	76501	25	18
	16.0	9369-FRBKB	4" diameter fan box, adjustable bar hanger, Speed Klamps™ - factory installed	1-¾	4	70 lb.	125 lb.	99739	20	28
	16.5	9373-FR	4" diameter thermoplastic fan box, ½" deep base, Speed Klamps™ - molded in, mounting hardware included	6 overall	4	70 lb.	110 lb.	78254	40	16
	22.5	9350-FANB	4" diameter fan box, adjustable bar hanger, Speed Klamps™ - factory installed, bulk packed	2-7/16	4	35 lb.	50 lb.	99021	20	32
	22.5	9350-KFR	4" diameter bottom mount, Speed Klamps™ - factory installed, mounting hardware included	2-7/16	4	35 lb.	50 lb.	10459	50	24
	22.5	9351-NFR	4" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-7/16	4	35 lb.	50 lb.	65001	50	27
	22.5	9351-NKFR	4" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-7/16	4	35 lb.	50 lb.	65002	50	28



All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Outlet Box
UL File No. E30594

Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED MOULDED PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9361-ESK	E168/7010-8/7020-8	N/A	N/A	N/A	N/A	N/A
9363-E	6060-02	N/A	N/A	N/A	N/A	N/A
9363-EK	6060-02	N/A	N/A	N/A	N/A	N/A
9363-EW	6010-402/6060-402	114-OW	N/A	N/A	N/A	N/A
9363-EWK	6010-402/6060-402	114-OW	N/A	N/A	N/A	N/A
9364	4060-02	N/A	N/A	N/A	N/A	N/A
9364-16/16K	4060-9402	N/A	N/A	N/A	N/A	N/A
9364-16G/16GK	N/A	N/A	N/A	N/A	N/A	N/A
9364-BH/BHK	4060-9502	N/A	N/A	N/A	N/A	N/A
9364-BHG/BHGK	N/A	N/A	N/A	N/A	N/A	N/A
9364-K	4060-02	N/A	N/A	N/A	N/A	N/A
9365-N	4160-C	N/A	N/A	N/A	N/A	N/A
9365-NK	4160-C/N40712RC	N/A	N/A	N/A	N/A	N/A
9366-EK	N/A	N/A	N/A	N/A	N/A	N/A
9366-EW	N/A	N/A	N/A	BH118R	N/A	N/A
9366-EWK	N/A	N/A	N/A	BH118R	N/A	N/A
9367-E	6000-402/E01-712	N/A	B117RSW	B117RSW	N/A	N/A
9367-EW	6000-402	N/A	B117RSW	B117RSW	N/A	N/A
9368-E	N/A	N/A	N/A	N/A	N/A	N/A
9368-EK	N/A	N/A	N/A	N/A	N/A	N/A
9368-EW	6070-4/E214	N/A	B120R	BH118R	EZ21S0	S118W
9368-EWK	6070-4/E214	N/A	B120R	BH118R	EZ21S0	S118W
9372-NMHK	N/A	N/A	N/A	N/A	N/A	N/A
RD-42	RD-30	N/A	B234ADJC/RDS-30	N/A	N/A	P242RRD
RD-42SS	N/A	N/A	N/A	N/A	N/A	P242SRD

fiberglassBOX™: Paddle Fan Support Boxes

Allied Moulded	Westinghouse	Arlington	Raco	Carlton PC	Steel City (T&B)	Carlton PH	Reiker (P&S)	Slater (P&S)
9335-NFR/NKFR	N/A	FB417S/FBS420S	N/A	N/A	N/A	N/A	N/A	N/A
9336-NKFR	01040-11	FBS415S	N/A	N/A	N/A	N/A	N/A	N/A
9350-FAN/FANB	N/A	N/A	927/928	N/A	N/A	4070-CFB-BHL	65521/85502	N/A
9350-FRBKOW	N/A	FBRS420R	934	N/A	N/A	N/A	22200	N/A
9350-KFR	N/A	FB423/FBS420	7120/299	B720-SHK	54171-CFB	CFB-16	44400/55528	S1-6-FAN
9351-NFR/NKFR	01240-11	FB417S	294-1	BH525L/BH525LP	54171-F-CFB	4170-CFB	55020/55025	S1-20-RFAN
9364-FAN/FANB	01525/ 01100/ 01010	N/A	925/926	MB715H	N/A	N/A	N/A	N/A
9364-FRBKOW	N/A	N/A	935	MB715RH	54151CFB-BHL-OW	N/A	33310/83300	N/A
9364-KFR	01050-11	FBS426	N/A	N/A	N/A	N/A	33303/55505	N/A
9365-NKFR	01250-11	N/A	N/A	BH525L	N/A	N/A	55015/33303	N/A
9369-FB	01020-11	FBS426	296-1	MB715S	54151-CFB	N/A	N/A	N/A
9369-FBH	01250	FBS415S	N/A	N/A	N/A	N/A	N/A	N/A
9369-FRBKB	0152511	FBRS415	926-1	MB715H	54151CFB-BHL	N/A	55501	N/A
9370-FR	01030	FB407	N/A	N/A	N/A	N/A	N/A	S1-09-FAN
9373-FR	02000	FB443	7120	CFB-16	N/A	N/A	N/A	S1-16-FAN
9375-FR	02525	FB442/FB412	7120	CFB-12	N/A	N/A	N/A	N/A