



93800S

MP400 BU (PK X 6)



Application: Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

Ballast Type: M59/O

Bulb: BT37

Color Temperature: 3600 K

Diameter: 4.60 IN

Initial Lumens: 40000

Length: 11.50 IN

Mean Design Lumens: 26000

Package Weight: 6.75 L

Shape: BT37

Type: Metal halide lamp HID

Voltage: 135 V

Warm Up Time: 41309

Average Life Hours: 20000

Base: Exclusionary Mogul (EX39)

Coating: PFA

CRI: 65

Effective Arc Length: 2

Lamp Type: Metal Halide

Light Center Length: 7 IN

Package (LxWxH): 14.25 IN x 9.50 IN x 12.25 IN

Pack By: 6

Special Features: Shatter-Resistant

UPC: 726585938001

Wattage: 400.0 W

ULEPH,ROHS,NSF Splash Zone



93800S

MP400 BU (PK X 6)



Application: Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

Ballast Type: M59/O

Bulb: BT37

Color Temperature: 3600 K

Diameter: 4.60 IN

Initial Lumens: 40000

Length: 11.50 IN

Mean Design Lumens: 26000

Package Weight: 6.75 L

Shape: BT37

Type: Metal halide lamp HID

Voltage: 135 V

Warm Up Time: 41309

Average Life Hours: 20000

Base: Exclusionary Mogul (EX39)

Coating: PFA

CRI: 65

Effective Arc Length: 2

Lamp Type: Metal Halide

Light Center Length: 7 IN

Package (LxWxH): 14.25 IN x 9.50 IN x 12.25 IN

Pack By: 6

Special Features: Shatter-Resistant

UPC: 726585938001

Wattage: 400.0 W

ULEPH,ROHS,NSF Splash Zone