


SINGLE-USE WIRE GRABBER™


Continued

SU 500 MCM




Code	Description	Qty.
98173	SU500MCM 14" wire lanyard	6
98174	SU500MCM 21" wire lanyard	6
98175	SU500MCM 28" wire lanyard	6
98176	SU500MCM 35" wire lanyard	6

SU 600 MCM



Code	Description	Qty.
98177	SU600MCM 14" wire lanyard	6
98178	SU600MCM 21" wire lanyard	6
98179	SU600MCM 28" wire lanyard	6
98180	SU600MCM 35" wire lanyard	6

SU 750 MCM



Code	Description	Qty.
98181	SU750MCM 14" wire lanyard	6
98182	SU750MCM 21" wire lanyard	6
98183	SU750MCM 28" wire lanyard	6
98184	SU750MCM 35" wire lanyard	6

SU 1000 MCM



Code	Description	Qty.
98185	SU1000MCM 14" wire lanyard	6
98186	SU1000MCM 21" wire lanyard	6
98187	SU1000MCM 28" wire lanyard	6
98188	SU1000MCM 35" wire lanyard	6

SINGLE-USE WIRE GRABBER™ LOAD CHART

WIRE GRABBER™ SPECIFICATIONS FOR COPPER & ALUMINUM WIRE											
Single-Use Wire Grabber™	Wire Size	Max Load (lbs)		Min conductor dia. (in)	Max conductor dia. (in)	Minimum EMT Conduit Size (in)					Crimper
		One Tool	Five Tools			1 Wire	2 Wires	3 Wires	4 Wires	5 Wires	
SU 8	8 AWG	130	650	0.134	0.146	-	-	-	-	-	12 to 15 ton Die Crimper or Dieless Crimper
SU 6	6 AWG	210	1050	0.169	0.184	-	-	-	-	-	
SU 4	4 AWG	300	1500	0.213	0.232	-	-	-	-	-	
SU 3	3 AWG	400	2000	0.238	0.260	-	-	-	-	-	
SU 2	2 AWG	500	2500	0.268	0.292	-	-	-	-	-	
SU 1	1 AWG	669	3345	0.299	0.332	-	-	-	-	-	
SU 1/0	1/0 AWG	844	4220	0.336	0.373	1	1-¼	1-¼	1-½	2	
SU 2/0	2/0 AWG	1000	5000	0.376	0.419	1	1-¼	1-½	2	2	
SU 3/0	3/0 AWG	1250	6250	0.423	0.470	1	1-½	1-½	2	2-½	
SU 4/0	4/0 AWG	1650	8250	0.475	0.528	1-¼	1-½	2	2	2-½	
SU 250	250 MCM	2000	10000	0.520	0.575	1-¼	2	2	2-½	2-½	
SU 300	300 MCM	2400	12000	0.570	0.631	1-¼	2	2	2-½	2-½	
SU 350	350 MCM	2400	12000	0.616	0.681	1-½	2	2-½	2-½	3	
SU 400	400 MCM	2400	12000	0.659	0.728	1-½	2-½	2-½	2-½	3	
SU 500	500 MCM	4000	20000	0.736	0.813	1-½	2-½	2-½	3	3-½	
SU 600	600 MCM	4200	21000	0.813	0.893	2	2-½	3	3	3-½	
SU 750	750 MCM	4300	21500	0.908	0.998	2	3	3	3-½	4	
SU 1000	1000 MCM	5000	25000	1.060	1.153	2	3	3-½	4	4-½	15 ton Die Crimper

For use on THHN & XHHN copper & aluminum wire only.

*May require special service (such as removing bushing and installing extra guide pulleys) when pulling Max diameter wires through Min size conduit.