



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A2011066 E1049 WHT M Instr *Crouse-Hinds*

Catalog Number	A2011066
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Roughneck E1049 Plug Insulator, Up to 1135A Continuous, 313-777 Kcmil, White, Hexagon Crimp or Solder, Male, Rubber, 1000 Vac/DC
Weight per unit	1.0 (lbs/each)
Product Category	Racks, Brackets, & Insulators

### Features

dimensions	11.0000 IN X 3.8500 IN X 3.3800 IN
Material	Rubber

### Dimensions and Weight

Size	3.00 In Diameter X 8.50 In Length
------	-----------------------------------

### Descriptions

Description	E1049 WHT M INSTR
extra long description	CRS-H A201106-6 E1049 M P INS 313MC
Features	Single conductor Roughneck high amperage connectors from Eaton's Crouse-Hinds Division are rugged and specifically designed for oil drilling applications. Weatherproof and providing a high level of indestructibility, the Roughneck connector offers the ultimate performance solution for safety and reliability challenges.
Long Description	Eaton Crouse-Hinds series Roughneck E1049 plug insulator, Up to 1135A continuous, 313-777 kcmil, White, Hexagon crimp or solder, Male, Rubber, 1000 Vac/dc
Product Type	E1049 M P Ins 313MCM to 777MCM WH
Special Features	NEMA 3 Enclosure

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662275107336
Manufacturers Part Number	A201106-6
UPC	662275107336

### Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Plug Insulator

### Packaging

Carton	1
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions .....	-40 To 125 Deg C
standard .....	UL (CANADA AND US)