



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A20H1606SSLP 20X16X6 N4X SS CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A20H1606SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 20X16X6, Brushed, SS304
Weight per unit	30.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	6
Height	20
Size	20.00x16.00x6.00 in
Width	16

Descriptions

Description	20X16X6 N4X SS CH CLMP CVR
extra long description	NVENT HOF A20H1606SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 20x16x6, Brushed, SS304
Product Type	Stainless Encl. 20.00X16.00X6.
Short Description	Stainless Encl. 20.00x16.00x6.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510240707
Manufacturers Part Number	A20H1606SSLP
UPC	783510240707

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	30

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X