



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996



A20H1608SSLP Wallmount, Hinged With Nema Clamps, Type 4X, 20X16 *Hoffman Enclosures, Inc.*

Catalog Number	A20H1608SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 20X16X8, Brushed, SS304
Weight per unit	33.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	8
Height	20
Size	20.00x16.00x8.00 in
Width	16

Descriptions

Description	WALLMOUNT, HINGED WITH NEMA CLAMPS, TYPE 4X, 20X16
extra long description	NVENT HOF A20H1608SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 20x16x8, Brushed, SS304
Product Type	Stainless Encl. 20.00X16.00X8.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510290207
Manufacturers Part Number	A20H1608SSLP
UPC	783510290207

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996

Packaging

Carton	1
Weight Per each	33

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant