



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A20R208HCR 20X20X8 N3R HC Encl

*Hoffman Enclosures, Inc.*

Catalog Number	A20R208HCR
Manufacturer	Hoffman Enclosures, Inc.
Description	Medium Drip-Shield Hinged-Cover Type 3R, 20.00X20.00X8.00, Gray, Steel
Weight per unit	35.0 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

### Features

ip rating	IP32
Material	MILD STEEL

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

### Dimensions and Weight

Depth	8
Height	20
Size	20.00x20.00x8.00 in
Width	20

### Descriptions

Description	20X20X8 N3R HC ENCL
extra long description	NVENT HOF A20R208HCR Enclosure 20.0
Features	Medium Drip-Shield Hinged-Cover, Type 3R, protects wiring and other electrical components in outdoor applications that require protection from rain, sleet, snow or dripping water. It offers the flexibility of securing enclosure with an optional padlock and collar studs for optional panel mounting. These enclosures have a size range of 16 x 12 x 6-in. to 60 x 36 x 12-in.
Long Description	Medium Drip-Shield Hinged-Cover Type 3R, 20.00x20.00x8.00, Gray, Steel
Product Type	Enclosure 20.00X20.00X8.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510386900
Manufacturers Part Number	A20R208HCR
UPC	783510386900



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall-Mounted / Pad-Mounted Enclosures

## Packaging

Carton	1
Weight Per each	35.04

## Uses, Certifications, and Standards

Application	Power Distribution; Controls and Drives
nema rating	3R Weather-resistant, except dust