



A242008LP 24X20X8 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A242008LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 24X20X8, Gray, Mild Steel
Weight per unit	51.8 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	8
Height	24
Size	24.00x20.00x8.00 in
Width	20

Descriptions

Description	24X20X8 N12 CH CLMP CVR
extra long description	NVENT HOF A242008LP Enclosure 24.00
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 24x20x8, Gray, Mild Steel
Product Type	Enclosure 24.00X20.00X8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510282004
Manufacturers Part Number	A242008LP
UPC	783510282004

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	51.84



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12