



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A242410LP 24X24X10 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A242410LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 12, 24X24X10, Gray, Mild Steel
Weight per unit	53.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP65
Material	MILD STEEL

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	10
Height	24
Size	24.00x24.00x10.00 in
Width	24

Descriptions

Description	24X24X10 N12 CH CLMP CVR
extra long description	NVENT HOF A242410LP Enclosure 24.00
Features	For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 12, 24x24x10, Gray, Mild Steel
Product Type	Enclosure 24.00X24.00X10.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510284008
Manufacturers Part Number	A242410LP
UPC	783510284008

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	53



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12 Indoor, dust-resistant