



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



A24H1608SSLP 24X16X8 N4X SS4 CH Clamp CVR

Hoffman Enclosures, Inc.

Catalog Number	A24H1608SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 24X16X8, Brushed, SS304
Weight per unit	39.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	8
Height	24
Size	24.00x16.00x8.00 in
Width	16

Descriptions

Description	24X16X8 N4X SS4 CH CLAMP CVR
extra long description	NVENT HOF A24H1608SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 24x16x8, Brushed, SS304
Product Type	Stainless Encl. 24.00X16.00X8.
Short Description	Stainless Encl. 24.00x16.00x8.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510240301
Manufacturers Part Number	A24H1608SSLP
UPC	783510240301

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Packaging

Carton	1
Weight Per each	39

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X