



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A36H30DLP 36X30X12 N4 CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A36H30DLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 36X30X12, Gray, Mild Steel
Weight per unit	95.0 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

ip rating	IP66
Material	MILD STEEL

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

### Dimensions and Weight

Depth	12
Height	36
Size	36.00x30.00x12.00 in
Width	30

### Descriptions

Description	36X30X12 N4 CH CLMP CVR
extra long description	NVENT HOF A36H30DLP Type 4 Encl. 36
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 36x30x12, Gray, Mild Steel
Product Type	Type 4 Encl. 36.00X30.00X12.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510246006
Manufacturers Part Number	A36H30DLP
UPC	783510246006

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	95

## Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12 Indoor, dust-resistant