



Part Number 10' LENGTHS	Part Number COILS	Part Number REELS	Trade Size	O.D.	I.D.
A51AE11 10' length	A51AEB1 200' length	A51AEQ1 1,500' length	1/2"	0.832" Min 0.848" Max	0.574" Min 0.630" Max
A51AG11 10' length	A51AGA1 100' length	A51AGJ1 1,000 length	3/4"	1.040" Min 1.060" Max	0.774" Min 0.834" Max
A51BA11 10' length	A51BAA1 100' length	A51BAN1 750' length	1"	1.305" Min 1.325" Max	0.999" Min 1.059" Max
A51BE11 10' length	Not Available	A51BEN1 750' length	1 1/2"	1.888" Min 1.912" Max	1.558" Min 1.622" Max

ETL LISTED

ETL CONTROL #3107144

CONFORMS TO UL1653

For use see NEC Article 362

Use only CANTEX No. 50 ENT Cement with this product

Not plenum rated

Red & Yellow colors available upon request

Not for exposed applications

May be used with SCH 40 PVC Couplings and fittings

600 Volt maximum

Not for direct bury

Minimum installation temperature -4°F (-20°C)

Maximum ambient temperature 122°F (50°C)

UL FT-4 Vertical Flame Test Rated



CANTEX

INC.

Fort Worth, TEXAS

EZ FLEX Type ENT
Electrical Nonmetallic Tubing

Drawn By: D. Gwinn

Date: 7/30/20

Ref. A51AE11