



Part Number 10' LENGTHS	Part Number COILS	Part Number REELS	Trade Size	O.D.	I.D.
A51AE11 10' length	A51AEB1 200' length	A51AEQ1 1,500' length	1/2"	0.832" Min 0.848" Max	0.574" Min 0.630" Max
A51AG11 10' length	A51AGA1 100' length	A51AGJ1 1,000 length	3/4"	1.040" Min 1.060" Max	0.774" Min 0.834" Max
A51BA11 10' length	A51BAA1 100' length	A51BAN1 750' length	1"	1.305" Min 1.325" Max	0.999" Min 1.059" Max

ETL LISTED
ETL CONTROL #3107144
CONFORMS TO UL1653
 For use see NEC Article 362
 Use only CANTEX No. 50 ENT Cement with this product
 Not plenum rated
 Red & Yellow colors available upon request
 Not for exposed applications
 May be used with SCH 40 PVC Couplings and fittings
 600 Volt maximum
 Not for direct bury
 Minimum installation temperature -4°F (-20°C)
 Maximum ambient temperature 122°F (50°C)
 UL FT-4 Vertical Flame Test Rated



CANTEX INC. Fort Worth, TEXAS		
EZ FLEX Type ENT Electrical Nonmetallic Tubing		
Drawn By: D. Gwinn	Date: 2/19/19	Ref. A51AE11