



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ACP1033CD 100A 3W3P P&S Plug (600VAC/250VDC) *Appleton/Oz Gedney*

Catalog Number	ACP1033CD
Manufacturer	Appleton/Oz Gedney
Description	Powertite Grounding Style 1 Clamping Ring Plug, Number Of Poles: 3, Number Of Wires: 3, Wire Size: 4 - 1 Awg (Building), 4 - 2 Awg (Extra Flex), Amperage Rating: 100 Amp, Voltage Rating: 600 Vac At 50 - 400 HZ, 250 VDC, Phase: 3 PH, Mat
Weight per unit	4.7 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	100
connection	Pressure Wire Terminal
Material	Copperfree (4/10 Of 1 PCT Maximum) Aluminum
Number of Wires	3
Phase	3
Poles	3
Voltage Rating	600 VAC At 50 - 400 HZ, 250 VDC
Wire Size	4 - 1

Descriptions

Description	100A 3W3P P&S PLUG (600VAC/250VDC)
extra long description	APP ACP1033CD 100A CLAMP RING PLUG
Long Description	Powertite Grounding Style 1 Clamping Ring Plug, Number Of Poles: 3, Number Of Wires: 3, Wire Size: 4 - 1 AWG (Building), 4 - 2 AWG (Extra Flex), Amperage Rating: 100 AMP, Voltage Rating: 600 VAC At 50 - 400 HZ, 250 VDC, Phase: 3 PH, Mat
Product Type	100A Clamp Ring Plug 3W3P ST1
Special Features	Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus;Grounding style: Shell only;Ideal for use on shipping docks, ports and other ship to shore applications;Locking screw and slot prevents plug cable collar from backing off;Natural finish glass filled polyester insulating blocks;Plug and receptacle combination is NEMA 4X rated when clamping ring is fully tightened on receptacle;Rough usag



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Appleton
GTIN	00781381440141
Manufacturers Part Number	ACP1033CD
UPC	781381440141

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 1 Clamping Ring Plug

Packaging

Carton	6
Weight Per each	4.71

Uses, Certifications, and Standards

Application	For ADR1033 Receptacle And ARC1033CD Connector Body
environmental conditions	Temperature Rating: -40 To 107 DEG C
nema rating	3, 3R, 4, 4X
standard	CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917