

Specifications



Eaton AH1201L

Eaton locking switch, #14-10 AWG, 15A, 120/277V, Back and side wiring, Key actuator, Maintained closure, Brown, Single-pole, Urea

General specifications

PRODUCT NAME	Eaton locking switch
CATALOG NUMBER	AH1201L
UPC	032664706271
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	1.05 in
PRODUCT WEIGHT	0.2 lb
COMPLIANCES	NAFTA
CERTIFICATIONS	cULus Listed UL Recognized
PRODUCT TYPE	Locking switch

Product specifications

ALLOWABLE WIRE SIZE #14-10 AWG

TORQUE RATING 14 lbf-inch

SPECIAL FEATURES Locking

TYPE Switch

AMPERAGE RATING 15A

VOLTAGE RATING 120/277 V

APPLICATION Industrial

WIRING METHOD Back and side

SWITCH TYPE Single-pole

CLOSURE TYPE Maintained

MATERIAL Urea

ACTUATOR Key

COLOR Brown

Resources

MULTIMEDIA

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AH1201L](#)

[Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

