

# Specifications



## Eaton AH1222W

Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Flush, 120/277V, Back and side, Screw, White, Double-Pole, Dual-pole, Brass, Polycarbonate

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart industrial grade toggle switch
<b>CATALOG NUMBER</b>	AH1222W
<b>UPC</b>	032664734762
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	1.005 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM Federal Specification Classification W-S-896E
<b>PRODUCT TYPE</b>	Industrial grade toggle switch



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Toggle switch
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	120/277 V
<b>NUMBER OF POLES</b>	Two-pole
<b>APPLICATION</b>	Industrial
<b>WIRING METHOD</b>	Back and side
<b>SWITCH TYPE</b>	Two-pole
<b>MOUNTING METHOD</b>	Flush
<b>CONNECTOR TYPE</b>	Screw
<b>MATERIAL</b>	Polycarbonate
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>TORQUE RATING</b>	14 lbf-inch
<b>TERMINAL ENCLOSURE MATERIAL</b>	Brass
<b>TERMINALS</b>	0.031 in
<b>COLOR</b>	White

## Resources

MULTIMEDIA	<a href="#">Arrow Hart - Connecting Safety to Reliability since 1890</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - AH1222W</a> <a href="#">Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

