



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH1995W Switch Toggle SP 3POS 20A 120/277V Mom WH *Eaton Wiring Devices*

Catalog Number	AH1995W
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Industrial Grade Toggle Switch, Momentary Toggle, #14-10 Awg, 20A, Flush, 120/277V, Side Wire, Screw, White, Load Type: Motor Control, Fan, Led, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, 1-Pole, 1-Pole, Brass
Weight per unit	N/A
Product Category	Disconnect Motor Switches

### Features

amperage rating	20
dimensions	1.3100 IN X 1.0000 IN X 3.2800 IN
media	Yes
Poles	Single-pole
Voltage Rating	120/277 V

### Descriptions

Description	SWITCH TOGGLE SP 3POS 20A 120/277V MOM WH
extra long description	EWD AH1995W Switch Tog SP 3Pos 20A
Features	Eaton's Arrow Hart broad line of extra heavy-duty industrial grade switches feature superior engineering, reliable performance and ease of installation. Available in toggle, lighted, pilot light, Corbin and locking versions.
Long Description	Eaton Arrow Hart industrial grade toggle switch, Momentary toggle, #14-10 AWG, 20A, Flush, 120/277V, Side wire, Screw, White, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, 1-pole, 1-pole, Brass
Product Type	Switch Tog SP 3POS 20A 120/277V Mom WH
Special Features	Momentary toggle

### Manufacturer Information

Brand	Eaton
GTIN	00040893643250
Manufacturers Part Number	AH1995W
UPC	040893643250

### Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Industrial grade toggle switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	50
Weight Per each	0

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
standard	cURus