

Eaton AH7810GD

Catalog Number: AH7810GD

Eaton manual motor controller, #14-10 AWG, 30A, Wall, 600V, Front wired screw and clamp, Maintained contact, Gray, NEMA 1, Enclosure: SS, Three-pole, Single-gang, Two-position, Three-phase, Toggle, Copper-alloy terminal, Single-throw

General specifications

| | |
|-------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton manual motor controller | AH7810GD |
| UPC | Product Length/Depth |
| 040893598604 | 4.75 in |
| Product Height | Product Width |
| 3.25 in | 3 in |
| Product Weight | Compliances |
| 1.6 lb | NAFTA |
| | RoHS Compliant |
| Certifications | |
| cULus Listed | |



Product specifications

Number of positions

2

Phase

Three-phase

Termination style

Front screw and clamp

Closure type

Maintained

Wiring method

Front wired screw and clamp

Enclosure

NEMA 1

Mounting method

Wall

Allowable wire size

#14-10 AWG

Amperage Rating

30A

Contact type

Maintained

Device grade

Industrial

NEMA Rating

1

Throw

Single-throw

Operating temperature

-20 to 65 °C

Terminals

Copper-alloy, brass screw

Voltage rating

600 V

Special features

With NEMA 1 enclosure

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Specifications and datasheets

[Eaton Specification Sheet - AH7810GD](#)

Switch type

Toggle switch

Color

Gray

Material

Glass-filled nylon

Number Of Poles

Three-pole

Number of gangs

1

Enclosure material

Stainless steel

Type

Manual motor controller

Application

Industrial



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)