

# Specifications



Photo is representative

## Eaton AHCL1130C

Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 30A, Industrial, 250 V, Back, Blue, Black, Ultra grip, Nylon, L11-30, Three-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)

### General specifications

|                      |                                                |
|----------------------|------------------------------------------------|
| PRODUCT NAME         | Eaton Arrow Hart Color Coded Locking Connector |
| CATALOG NUMBER       | AHCL1130C                                      |
| UPC                  | 032664759956                                   |
| PRODUCT LENGTH/DEPTH | 2.23 in                                        |
| PRODUCT HEIGHT       | 3.71 in                                        |
| PRODUCT WIDTH        | 2.1 in                                         |
| PRODUCT WEIGHT       | 0.001 lb                                       |
| COMPLIANCES          | RoHS Compliant                                 |
| CERTIFICATIONS       | cULus Listed<br>NOM                            |
| PRODUCT TYPE         | Color Coded Locking                            |

## Product specifications

|                              |                                                         |
|------------------------------|---------------------------------------------------------|
| <b>SPECIAL FEATURES</b>      | Voltage Color Coding                                    |
| <b>TYPE</b>                  | Locking Connector                                       |
| <b>AMPERAGE RATING</b>       | 30A                                                     |
| <b>VOLTAGE RATING</b>        | 3Ø 250 V                                                |
| <b>APPLICATION</b>           | Industrial                                              |
| <b>WIRING METHOD</b>         | Back                                                    |
| <b>NUMBER OF WIRES</b>       | 3                                                       |
| <b>NUMBER OF POLES</b>       | Three-pole                                              |
| <b>COLOR</b>                 | Blue<br>Black                                           |
| <b>CORD DIAMETER</b>         | 0.38-1 in (9.5-25.4 mm)                                 |
| <b>MATERIAL</b>              | Nylon                                                   |
| <b>OPERATING TEMPERATURE</b> | -40 to 60 °C (-40 to 140 °F)                            |
| <b>ALLOWABLE WIRE SIZE</b>   | #14-8 AWG                                               |
| <b>NEMA CONFIGURATION</b>    | L11-30                                                  |
| <b>TORQUE RATING</b>         | For #10-14 AWG: 14-16 lbf-inch. For #8 AWG: 20 lbf-inch |
| <b>DESIGN TYPE</b>           | Ultra grip                                              |
| <b>FACE/BODY MATERIAL</b>    | Nylon                                                   |

## Resources

|                               |                                                                                                                                                    |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| MULTIMEDIA                    | <a href="#">Eaton Arrow Hart color coded locking devices</a>                                                                                       |
| SPECIFICATIONS AND DATASHEETS | <a href="#">Eaton Specification Sheet - AHCL1130C</a><br><a href="#">Arrow Hart color coded industrial grade L11-30 locking devices spec sheet</a> |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

