



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AHCL2120C CCL Conn 20A 120/208V 3PH 4P5W-BL&BK *Eaton Wiring Devices*

Catalog Number	AHCL2120C
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Color Coded Locking Connector, #14-8 Awg, 20A, Industrial, 3ØY 120/208 V, Back, Blue, Black, Ultra Grip, Nylon, L21-20, Four-Pole, Five-Wire, Nylon, 0.38 - 1.16" (9.5 - 29.5MM)
Weight per unit	10.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

media	Yes
-------	-----

Descriptions

Description	CCL CONN 20A 120/208V 3PH 4P5W-BL&BK
extra long description	EWD AHCL2120C CCL Conn 20A 120/208V
Features	Eaton's Arrow Hart color coded locking devices are an industry-first solution that adds six voltage rating color codes consistent with IEC 60309 standards to locking plugs, connectors, inlets, outlets and receptacles to provide you a quick, clear and easy way to identify your circuit voltage. Available in standard NEMA configurations for 20A and 30A applications, the devices ensure long-lasting, dependable service in the most demanding environments, are built with a contemporary flare and ergonomic design
Long Description	Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 20A, Industrial, 3ØY 120/208 V, Back, Blue, Black, Ultra grip, Nylon, L21-20, Four-pole, Five-wire, Nylon, 0.38 - 1.16" (9.5 - 29.5mm)
Product Type	CCL Conn 20A 120/208V 3PH 4P5W-BL&BK
Special Features	Industrial grd plugs & conns

Manufacturer Information

Brand	Eaton
GTIN	00032664755613
Manufacturers Part Number	AHCL2120C
UPC	032664755613

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
----------------------	----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	40
Weight Per each	10