

# Eaton AHG22111

Catalog Number: AHG22111

Eaton Crouse-Hinds series AHG flexible fixture hanger, 16-30 lb, 3/4" luminaire stem size, Feraloy iron alloy, Pendant mount, 3/4" nipple size, Cushion type



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series AHG flexible fixture hanger	AHG22111
	UPC
	782274027401
Product Length/Depth	Product Height
3.25 in	3.88 in
Product Width	Product Weight
4 in	2.25 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 2

Class II, Division 2

Class III

### NEMA Rating

3

3R

## Product specifications

### Type

Cushion

### Mounting Type

Pendant

### Luminaire stem size

3/4"

### Nipple size

3/4"

### Luminaire rated weight

16-30 lb

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series Ball or Cushion Hazardous Area Flexible Fixture Hangers catalog page](#)

### Certification reports

[Ball or Cushion Hazardous Area Flexible Fixture Hangers Canadian certification](#)

[Ball or Cushion Hazardous Area Flexible Fixture Hangers UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - AHG22111](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)