



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYCL153PHWH Ariadni 150W Led 3WAY White Clam

Lutron

Catalog Number	AYCL153PHWH
Manufacturer	Lutron
Description	Dimmable Bulb, Toggle Switch Type, 120 V, 150 W;6000 W, 60 HZ, Incandescent/Halogen;Dimmable CFL/Led Lamp, Motion Sensor, Wall Mount, 2.86 In Length, 2.58 In Width, 4.60 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.4 LB/Ea
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Toggle Switch
connection	Screw Terminal
Connection Type	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
Poles	1
Voltage Rating	120
Wattage	600

Material, Color, and Finish

Finish	Gloss
--------	-------

Dimensions and Weight

Size	4.60 x 2.86;117 x 73
------	----------------------

Descriptions

Description	ARIADNI 150W LED 3WAY WHITE CLAM
extra long description	LUT AYCL-153PH-WH ARIADNI CFL/LED D
Special Features	Controls 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Toggle turn lights on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs as well as halogens and incandescents.

Manufacturer Information

GTIN	00027557826006
UPC	027557826006

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Preset dimmer, 3-way/single-pole, clamshell packaging



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	3
Package	48
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL1472 CSA C22.2 184.1, NOM