



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYCL153PHWH Ariadni 150W Led 3WAY White Clam *Lutron*

Catalog Number	AYCL153PHWH
Manufacturer	Lutron
Description	Dimmable Bulb, Toggle Switch Type, 120 V, 150 W;6000 W, 60 HZ, Incandescent/Halogen;Dimmable CFL/Led Lamp, Motion Sensor, Wall Mount, 2.86 In Length, 2.58 In Width, 4.60 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.4 LB/Ea
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting Dimmers

Features

Connection Type	Screw Terminal
insulation	Plastic
Poles	1
Voltage Rating	120
Wattage	600

Material, Color, and Finish

Finish	Gloss
--------	-------

Dimensions and Weight

Size	4.60 x 2.86;117 x 73
------	----------------------

Descriptions

Description	ARIADNI 150W LED 3WAY WHITE CLAM
extra long description	LUT AYCL-153PH-WH ARIADNI CFL/LED D
Special Features	Controls 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Toggle turn lights on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs as well as halogens and incandescents.

Manufacturer Information

GTIN	00027557826006
UPC	027557826006

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Preset dimmer, 3-way/single-pole, clamshell packaging

Packaging

Carton	3
Package	48
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
standard	UL1472 CSA C22.2 184.1, NOM