



Shown actual size: Ariadni® preset dimmer and 1-gang Fassada® wallplate in white (WH)

available models

source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- fluorescent lighting
- LED lighting
- quiet 3-speed fan controls
- quiet 3-speed fan/light controls

control locations

- single pole (one location)
- 3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

- | | |
|------------------|------------------------|
| WH white | LA light almond |
| IV ivory | BR brown |
| AL almond | BL black |

Ariadni® dimmers

product family features

- matches existing switches
- toggle-style switch returns light to suit any activity
- slide adjusts light to your favorite level
- coordinating Fassada® wallplates available separately (including matte, gloss, and stainless steel finishes)
- **eco-dim**® model available

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com

dimmers



- toggle turns on/off
- slide up to brighten, down to dim
- eco-dim® model guarantees at least 15% energy savings compared to a standard switch

incandescent/halogen

single pole	600W	AY-600P-
single pole	1000W	AY-10P-
3-way	600W	AY-603P-
3-way	1000W	AY-103P-

incandescent/halogen — eco-dim®†

NEW

single pole/3-way	600W	AY-603PG-
-------------------	------	------------------

magnetic low-voltage

single pole	600 VA (450 W)	AYLV-600P-
3-way	600 VA (450 W)	AYLV-603P-

Suggested maximum lighting load for magnetic low-voltage dimming is 450W for 600VA products to allow for transformer losses.

† available in white, ivory, almond, and light almond

dimmers with locator light



- toggle turns on/off
- slide up to brighten, down to dim
- includes locator light
- not available in black

incandescent/halogen

single pole	600W	AY-600PNL-
single pole	1000W	AY-10PNL-
3-way	600W	AY-603PNL-
3-way	1000W	AY-103PNL-

See page 95 for available colors.

To order, add color suffix to model number.

Example: **AY-600P- WH**

fluorescent dimming with Hi-lume®, Compact SE™, Eco-10®, EcoSystem® ballasts, and **Hi-lume® LED**



- use with Lutron® 3-wire line-voltage control electronic dimming ballasts
- please refer to the Lutron® Fluorescent Dimming Systems Selection Guide (P/N 366-002) for more information
- no derating if ganged

fluorescent*

single pole/3-way 120V	8A	AYF-103P-	
single pole/3-way 277V	6A	AYF-103P-277-	

LED with Hi-lume® LED driver only* NEW

single pole/3-way 120V	8A	AYF-103P-	
single pole/3-way 277V	6A	AYF-103P-277-	

LED with GRX-TVI (0-10 VDC sink control)* NEW

single pole/	16A load	AYF-103P-	
3-way	30 mA control		
	120/277V		

* requires neutral wire connection

See page 95 for available colors.
To order, add color suffix to model number.
Example: **AY-103P- WH**

fan control



- toggle turns on/off
- slide up to increase speed, down to decrease
- 3 quiet fan speeds for increased comfort
- for use with only one ceiling paddle fan

quiet 3-speed control

single pole/3-way 1.5A

AYFSQ-F-

fan/light control



fan control (left)

- slide up to on/increase fan speed, down to off/decrease fan speed
- 3 quiet fan speeds for increased comfort
- designed to reduce motor hum
- for use with only one ceiling paddle fan

dimmer (right)

- toggle turns light on/off
- right slider up to brighten, down to dim

quiet 3-speed control & dimmer

single pole fan control 1.5A (left)

AY2-LFSQ-

single pole dimmer 300W (right)

See page 95 for available colors.

To order, add color suffix to model number.

Example: **AYFSQ-F- WH**