



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3315 Park Place
75462-0000, TX Paris
Phone: 903-784-1916
Fax: 903-784-0107



BAB1020 Type Bab Circuit BRKR 1P, 20AMP 120/240V, 10, 000AIC, *Eaton Corp*

Catalog Number	BAB1020
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 20 A, Bolt-On, 120/240 V Ac, 4.8 In Overall Height, 3.7 In Overall Length, 1.2 In Overall Width, 2 LB
Weight per unit	2.9 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	3.0000 IN X 1.0000 IN X 2.5000 IN
media	Yes
Poles	Single-pole

Descriptions

Description	TYPE BAB CIRCUIT BRKR 1P,20AMP 120/240V,10,000AIC,
extra long description	ETN BAB1020 BAB 1P,20AMP, 120/240V,
Special Features	Bolt-on mountingHigh intensity discharge

Manufacturer Information

GTIN	00786679301203
UPC	786679301203

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	24
Weight Per each	2.9

Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified,UL Listed