



BAB1040 Type Bab Circuit BRKR 1P 40AMP, 40C, 120/240V, 10, 000

Eaton Corp

Catalog Number	BAB1040
Manufacturer	Eaton Corp
Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-Pole, Non-Interchangeable, 40A, 10 Kaic, 120/240V
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	3.6000 IN X 1.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE BAB CIRCUIT BRKR 1P 40AMP,40C,120/240V,10,000
extra long description	ETN BAB1040 BAB bkr, 1P, 40AMP,40C,
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 40A, 10 kaic, 120/240V
Product Type	Bab BKR, 1P, 40AMP, 40C, 120/240V, 10ka

Manufacturer Information

Brand	Eaton
GTIN	00786679301401
Manufacturers Part Number	BAB1040
UPC	786679301401

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	24
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2001 ATKINSON DRIVE
75901-0000, TX Lufkin
Phone: 936-632-9733
Fax: 936-632-9736

Uses, Certifications, and Standards

Application

standard

Marine Vessels and Equipment - Marine Vessels and Equipment - Other
Datacenters - IT Space: CI and Hyper
ConvergedOtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities
- Other
CSA Certified, UL Listed