



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BFV108Q Highland Vinyl Ins Block Fork Term, 12-10awg *Minnesota Mining (3M)*

| | |
|------------------|---|
| Catalog Number | BFV108Q |
| Manufacturer | Minnesota Mining (3M) |
| Description | Block Fork, #12 Awg Conductor Size, #10 Awg Conductor Size, Insulated, Vinyl Insulation Material, Copper Conductor Material, Yellow Insulation Color, 600 V (Building Wiring);1000 V (Signs/Fixture), -40 °F Operating Temperature, +221 °F Operating Temperature, 1.03 In Overall Length, Block Fork Terminal, 0.11 LB |
| Weight per unit | 0.1100 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Descriptions

| | |
|------------------------|--|
| Description | HIGHLAND VINYL INS BLOCK FORK TERM, 12-10AWG |
| extra long description | 3M 7000133647 3M™ Highland™ Vinyl I |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Highland |
| GTIN | 00051128599891 |
| Manufacturers Part Number | BFV108Q |
| UPC | 051128599891 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | TERMINALS |
| Type | Butted |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.11 |

Uses, Certifications, and Standards

| | |
|----------|------------|
| standard | UL and CSA |
|----------|------------|