

# Eaton BR2020B100

Catalog Number: BR2020B100

Eaton BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 100A, single-phase, 20-pole, 20 circuits, 20 spaces, 120/240V, #4-1/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c2 box size



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BR2020B100
<b>UPC</b>	<b>Product Length/Depth</b>
786676444156	24.75 in
<b>Product Height</b>	<b>Product Width</b>
4.25 in	16 in
<b>Product Weight</b>	<b>Warranty</b>
23.49 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## Product specifications

### Special features

No feed-thru lugs

### Type

Main circuit breaker

### Amperage Rating

100 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

20

### Number of spaces

20

### Phase

Single-phase

### Wire size

#4-1/0 AWG Cu/Al

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

C2

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BR2020B100](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)