



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR2024N125

UPC:786676448253

Dimensions:

- **Height:** 23 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Notes:The maximum rating of the panel is the main breaker rating when used as service entrance equipment. Has notch for brhdk125 hold-down kit.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs, includes BREQS125 hold-down screw
- **Type:** Convertible main
- **Amperage Rating:** 125A
- **Box Size:** C2
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Combination
- **Number Of Circuits:** 24
- **Number Of Spaces:** 20
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** Determined by circuit breaker installed

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER,](#)



BR CONVERTIBLE, INDOOR NEMA 1,
120/240 VAC, 1 PHASE

- Eatons Volume 1-Residential and Light Commercial
- Cutler-Hammer Type CH and BR Loadcenters - Instructions
- Type BR Arc Fault Circuit Breakers and Loadcenters
- Eaton Specification Sheet - BR2024N125

Certifications:

- UL 50
- UL 67

Product compliance: No Data