



Powering Business Worldwide

pe.eaton.com

Eaton BR style 1-inch loadcenter

BR2030B150

UPC:786676444903

Dimensions:

- **Height:** 27 IN
- **Length:** 3.9 IN
- **Width:** 14.39 IN

Weight:36 LB

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 150A
- **Box Size:** C4
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 30
- **Number Of Spaces:** 20
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2/0 AWG-300 kcmil Cu/Al
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- Eatons Volume 1-Residential and Light Commercial
- Cutler-Hammer Type CH and BR Loadcenters - Instructions
- Type BR Arc Fault Circuit Breakers and Loadcenters
- Eaton Specification Sheet - BR2030B150

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.