



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR2040L200G 20/40C 200A Mlo Loadcenter W/Bonded Ground Bar

Eaton Corp

| | |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | BR2040L200G |
| Manufacturer | Eaton Corp |
| Description | BR Style 1-Inch Loadcenter, Main Lug, Ground Bar, Includes BREQS125 Hold-Down Screw, 200A, Single-Phase, 40-Pole, 40 Circuits, 20 Spaces, 120/240V, #1-300 Kcmil Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, C2 Box Size |
| Weight per unit | 22.4 (lbs/each) |
| Product Category | Single Phase Main Lug Load Cen |

Features

| | |
|----------------------|-----------------------------------------------------------------------------------------------------------|
| amperage rating | 59120 |
| Box Size | QUARTZ LIGHTING LENS, GLASS LENS REFRACTOR/LENS TYPE; QF500F QUARTZ FLOODLIGHT FIXTURE TYPE; RAB[R] BRAND |
| cover | Cover included |
| Cover Type | Cover included |
| dimensions | 98.5520millimetreX36.3474centimetreX58.4200centimetre |
| interrupt rating | 25 kAIC |
| main circuit breaker | BWH |
| Number of Circuits | 40 DEG C |
| number of spaces | 20 W |
| Number of Wires | Three-wire |
| Phase | 1 PH |
| used with | Type BR 1-inch breakers |
| Voltage Rating | 120/240 VAC |
| Wire Size | #1-300 kcmil Cu/Al at 60°C or 75°C |

Material, Color, and Finish

| | |
|--------------------|----------|
| Bus Material | Aluminum |
| Enclosure Material | Metallic |

Dimensions and Weight

| | |
|------|----|
| Size | C2 |
|------|----|

Descriptions

| | |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 20/40C 200A MLO LOADCENTER W/BONDED GROUND BAR |
| extra long description | ETN BR2040L200G BR style 1-inch loa |
| Long Description | BR style 1-inch loadcenter, main lug, ground bar, includes BREQS125 hold-down screw, 200A, single-phase, 40-pole, 40 circuits, 20 spaces, 120/240V, #1-300 kcmil Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c2 box size |
| Product Type | BR Style 1-Inch Loadcenter |
| Special Features | Ground bar, includes BREQS125 hold-down screw |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786676003490 |
| Manufacturers Part Number | BR2040L200G |
| UPC | 786676003490 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category Description | LOADCENTERS & COVERS |
| igcc | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type | MAIN LUG |
| unspsc code | 39121101 |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 22.4 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------|
| Application | Power Distribution |
| Enclosure | NEMA 1 |
| Mounting | Combination |
| standard | UL 67;UL 50 |