


Straight Blade Receptacles Commercial Specification Grade Receptacles

15 & 20A, 125V

Pass & Seymour



Features	
<ul style="list-style-type: none"> Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. 	<ul style="list-style-type: none"> CR Series: #14 – #10 AWG solid side wire only. BR Series: side and internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment. Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.



CR15I

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance	
	A.	V.			UL498	C22.2 No. 42
Duplex Receptacles Side Wire						
CR15I	15	125	Ivory	5-15R	•	•
CR15W	15	125	White	5-15R	•	•
CR15	15	125	Brown	5-15R	•	•
CR15GRY	15	125	Gray	5-15R	•	•
CR15LA	15	125	Light Almond	5-15R	•	•
CR20I	20	125	Ivory	5-20R	•	•
CR20W	20	125	White	5-20R	•	•
CR20	20	125	Brown	5-20R	•	•
CR20GRY	20	125	Gray	5-20R	•	•
CR20BK	20	125	Black	5-20R	•	•
CR20RED	20	125	Red	5-20R	•	•
CR20LA	20	125	Light Almond	5-20R	•	•
Duplex Receptacles Back & Side Wire						
BR15I	15	125	Ivory	5-15R	•	•
BR15W	15	125	White	5-15R	•	•
BR15	15	125	Brown	5-15R	•	•
BR15GRY	15	125	Gray	5-15R	•	•
BR15LA	15	125	Light Almond	5-15R	•	•
BR20I	20	125	Ivory	5-20R	•	•
BR20W	20	125	White	5-20R	•	•
BR20	20	125	Brown	5-20R	•	•
BR20GRY	20	125	Gray	5-20R	•	•
BR20BK	20	125	Black	5-20R	•	•
BR20LA	20	125	Light Almond	5-20R	•	•

NEW

NEW

2 Pole, 3 Wire



NEMA 5-15R



NEMA 5-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Straight Blade Receptacles Commercial Specification Grade Receptacles

15 & 20A, 125V

Pass & Seymour



Features	
<ul style="list-style-type: none"> Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. 	<ul style="list-style-type: none"> CR Series: #14 – #10 AWG solid side wire only. BR Series: side and internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment. Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.



CR15I

Catalog Number	Rating		Color	NEMA Config. No.	3rd Party Compliance	
	A.	V.			UL498	C22.2 No. 42
Duplex Receptacles Side Wire						
CR15I	15	125	Ivory	5-15R	•	•
CR15W	15	125	White	5-15R	•	•
CR15	15	125	Brown	5-15R	•	•
CR15GRY	15	125	Gray	5-15R	•	•
CR15LA	15	125	Light Almond	5-15R	•	•
CR20I	20	125	Ivory	5-20R	•	•
CR20W	20	125	White	5-20R	•	•
CR20	20	125	Brown	5-20R	•	•
CR20GRY	20	125	Gray	5-20R	•	•
CR20BK	20	125	Black	5-20R	•	•
CR20RED	20	125	Red	5-20R	•	•
CR20LA	20	125	Light Almond	5-20R	•	•
Duplex Receptacles Back & Side Wire						
BR15I	15	125	Ivory	5-15R	•	•
BR15W	15	125	White	5-15R	•	•
BR15	15	125	Brown	5-15R	•	•
BR15GRY	15	125	Gray	5-15R	•	•
BR15LA	15	125	Light Almond	5-15R	•	•
BR20I	20	125	Ivory	5-20R	•	•
BR20W	20	125	White	5-20R	•	•
BR20	20	125	Brown	5-20R	•	•
BR20GRY	20	125	Gray	5-20R	•	•
BR20BK	20	125	Black	5-20R	•	•
BR20LA	20	125	Light Almond	5-20R	•	•

NEW

NEW

2 Pole, 3 Wire



NEMA 5-15R



NEMA 5-20R

For Configurable Solutions, see Page U-1.