



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR240B Type BR BRKR 40A/2 Pole 120/240V 10K

Eaton Corp

Catalog Number	BR240B
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, Tapped Molded Opening, Special Application, 40 A, 10 Kaic, Two-Pole, 120/240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	0.6000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Descriptions

Description	TYPE BR BRKR 40A/2 POLE 120/240V 10K
extra long description	ETN BR240B Type BR Breaker 40A/2 Po
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, Tapped molded opening, special application, 40 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	Type BR Breaker 40A/2 Pole 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676003582
Manufacturers Part Number	BR240B
UPC	786676003582

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
----------------------	---------------------------------------------

Packaging

Carton	1
Weight Per each	0.6