



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR3040B200V4 30/40C 200A 1PH MB Loadcenter Value Pack

Eaton Corp

Catalog Number	BR3040B200V4
Manufacturer	Eaton Corp
Description	BR Style Load Center, 30 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material
Weight per unit	37.2 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	59120
Box Size	QUARTZ LIGHTING LENS, GLASS LENS REFRACTOR/LENS TYPE; QF500F QUARTZ FLOODLIGHT FIXTURE TYPE; RAB[R] BRAND
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX58.4200centimetre
main circuit breaker	BWH
number of spaces	30 W
Number of Wires	Three-wire
Phase	1 W
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	C2
------	----

Descriptions

Also Known As...	panel board Fuse box panel breaker panel load center electric panel panelboard breaker box
Description	30/40C 200A 1PH MB LOADCENTER VALUE PACK
extra long description	ETN BR3040B200V4 BR style 1-inch lo

Manufacturer Information

GTIN	00782113491653
UPC	782113491653



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	Main circuit breaker
unspsc code	39121101

Packaging

Carton	1
Weight Per each	37.18

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting	Combination
standard	UL 67;UL 50