

# Eaton BR3040N200R

Catalog Number: BR3040N200R

Eaton BR convertible loadcenter, Value pack, Convertible main, 200 A, D1r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 40 Circuits, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V, Determined by circuit breaker installed



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR convertible loadcenter	BR3040N200R
<b>UPC</b>	<b>Product Length/Depth</b>
786676448901	5.19 in
<b>Product Height</b>	<b>Product Width</b>
34 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
40 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

## Product specifications

### Special features

Value pack

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Number of circuits

40

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

Determined by circuit breaker installed

### Box size

D1R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BR3040N200R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BR3040N200R

Catalog Number: BR3040N200R

Eaton BR convertible loadcenter, Value pack, Convertible main, 200 A, D1r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 40 Circuits, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V, Determined by circuit breaker installed



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR convertible loadcenter	BR3040N200R
<b>UPC</b>	<b>Product Length/Depth</b>
786676448901	5.19 in
<b>Product Height</b>	<b>Product Width</b>
34 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
40 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

## Product specifications

### Special features

Value pack

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Number of circuits

40

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

Determined by circuit breaker installed

### Box size

D1R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BR3040N200R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)