



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR3042L125 30/42CT 125A Mlo 1PH LDCTR N1

*Eaton Corp*

Catalog Number	BR3042L125
Manufacturer	Eaton Corp
Description	BR Style 1 In Loadcenter, Split Neutral, Nema 1 Enclosure, Single-Phase, Three-Wire, 30 Spaces, 42 Circuits, Box: D1, Aluminum Bus
Weight per unit	10.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

### Features

amperage rating	125 VAC
Box Size	LIGHTING TRACK, MINIATURE TYPE; EXTRUDED ALUMINUM MATERIAL; SATIN WHITE FINISH; 90-5/8 INCH; 1-3/8 INCH; 11/16 INCH; 8 FT NOMINAL LENGTH; UL, CSA APPROVAL; 20 AMPERE CURRENT RATING; 2 CIRCUIT(S); HALO[R], POWER-TRAC BRAND; WALL THICKNESS 0.06 INCH
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX73.9902centimetre
Number of Circuits	42 W
number of spaces	30 W
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1 in breakers
Voltage Rating	120/240 VAC
Wire Size	#6-2/0 Cu/Al at 60°C or 75°C

### Material, Color, and Finish

Bus Material	Aluminum
Enclosure Material	Metallic

### Dimensions and Weight

Size	F3003/4 YL105
------	---------------

### Descriptions

Description	30/42CT 125A MLO 1PH LDCTR N1
extra long description	ETN BR3042L125 BR Style 1 in Loadce
Long Description	BR Style 1 in Loadcenter, Split neutral, NEMA 1 enclosure, Single-phase, Three-wire, 30 spaces, 42 circuits, Box: D1, Aluminum bus
Product Type	BR Style 1 In Loadcenter



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685857060
Manufacturers Part Number	BR3042L125
UPC	786685857060

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMESELECT[T] BRAND
Type	Split neutral
unspsc code	39121101

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	10

## Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
standard	UL 67;UL 50