

Eaton BR3060BQN150

Catalog Number: BR3060BQN150

BR loadcenter, 150A CSR MAIN BREAKER, 30 SPACES/60 CIRCUITS, 120/240V, ALUMINUM BUS, G1 INDOOR BOX SIZE, #2-300MCM INCOMING LUG SIZE, QUICK CONNECT NEUTRAL CONFIGURATION

General specifications



Product Name	Eaton BR main breaker loadcenter	Catalog Number	BR3060BQN150
UPC	786676026277	Product Length/Depth	3.88 in
Product Height	34.13 in	Product Width	14.31 in
Product Weight	34 lb	Warranty	10 year

Product specifications

Special features

QUICK CONNECT NEUTRALS

Type

Main circuit breaker

Amperage Rating

150 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

60

Number of spaces

30

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

G1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Specifications and datasheets

Eaton Specification Sheet - BR3060BQN150

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BR3060BQN150

Catalog Number: BR3060BQN150

BR loadcenter, 150A CSR MAIN BREAKER, 30 SPACES/60 CIRCUITS, 120/240V, ALUMINUM BUS, G1 INDOOR BOX SIZE, #2-300MCM INCOMING LUG SIZE, QUICK CONNECT NEUTRAL CONFIGURATION

General specifications



Product Name	Eaton BR main breaker loadcenter	Catalog Number	BR3060BQN150
UPC	786676026277	Product Length/Depth	3.88 in
Product Height	34.13 in	Product Width	14.31 in
Product Weight	34 lb	Warranty	10 year

Product specifications

Special features

QUICK CONNECT NEUTRALS

Type

Main circuit breaker

Amperage Rating

150 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

60

Number of spaces

30

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

G1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR3060BQN150](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)