

Specifications



Eaton BR3060NQN200

BR style 1-inch loadcenter, convertible main, ground bar, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, depends upon main breaker kit or main lug kit chosen., NEMA 1 enclosure, 11 box size

Product specifications

AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MOUNTING	Combination
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
WIRE SIZE	Determined by circuit breaker installed
BOX SIZE	G1
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BR3060NQN200
UPC	786676026369
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	34.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	34 lb
WARRANTY	10 year
CATALOG NOTES	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

EATON

Powering Business Worldwide

Specifications



Eaton BR3060NQN200

BR style 1-inch loadcenter, convertible main, ground bar, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, depends upon main breaker kit or main lug kit chosen., NEMA 1 enclosure, 11 box size

Product specifications

AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MOUNTING	Combination
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
WIRE SIZE	Determined by circuit breaker installed
BOX SIZE	G1
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BR3060NQN200
UPC	786676026369
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	34.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	34 lb
WARRANTY	10 year
CATALOG NOTES	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

EATON

Powering Business Worldwide