

Eaton BR3060NQN200

Catalog Number: BR3060NQN200

BR style 1-inch loadcenter, convertible main, ground bar, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, depends upon main breaker kit or main lug kit chosen., NEMA 1 enclosure, I1 box size

General specifications



Product Name	Catalog Number
Eaton BR convertible loadcenter	BR3060NQN200
UPC	Product Length/Depth
786676026369	3.88 in
Product Height	Product Width
34.13 in	14.31 in
Product Weight	Warranty
34 lb	10 year

Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Product specifications

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Mounting

Combination

Number of circuits

60

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

G1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Specifications and datasheets

Eaton Specification Sheet - BR3060NQN200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)